



## CLC BIN WASHER

Safe, consistent  
& easy to operate.



Our tilting door cabinet washer features effortless loading and unloading and repeatable cost-effective washing of your equipment. The washer is programmable via HMI to suit the type of tubs and required washing cycles. The touchscreen controlled PLC optimizes energy, water and detergent consumption while ensuring safe operation.

- ◆ Sanitary construction in 304 or 316 stainless steel
- ◆ Spray headers cover the entire wash area
- ◆ Closed-cycle conductivity analysis for water and detergent recycling
- ◆ Tubs are tilted during wash cycles ensuring self-draining for a proper wash every time
- ◆ Water level and temperature control
- ◆ Pre-wash rotary filter eliminates waste and particulate from the wash water
- ◆ Wedge wire filtration removes smaller particles during wash cycle
- ◆ Self-cleaning

**24/7  
Emergency  
Service**

1.888.339.3801  
[info@qualtechgroup.com](mailto:info@qualtechgroup.com)

# Specifications:



MODEL	NUMBER OF BINS	A (in)	B (in)	C (in)	D (in)
CLC01-11	1	109	142	206	114
CLC01-12	2	149	142	206	114

CLC01		Configuration choice		Code	
Bin type		Plastic bin	<input checked="" type="checkbox"/>	1	Ⓐ
		Euro bin	<input type="checkbox"/>	2	
		Cheese cart	<input type="checkbox"/>	3	
		Vat	<input type="checkbox"/>	4	
		Other	<input type="checkbox"/>	5	
Number of bins		1	<input type="checkbox"/>	1	Ⓑ
		2	<input checked="" type="checkbox"/>	2	
Washing cycle <sup>1</sup>		Pre-wash / Wash / Rinse	<input checked="" type="checkbox"/>	3	Ⓒ
		Pre-wash / Wash / Rinse / Sanitation	<input type="checkbox"/>	4	
Heating <sup>2</sup>		Tubular heat exchanger - Water	<input type="checkbox"/>	1	Ⓓ
		Tubular heat exchanger - Steam	<input type="checkbox"/>	2	
		Electric element	<input checked="" type="checkbox"/>	3	
Electrical supply		460V / 3ph / 60Hz	<input type="checkbox"/>	43	Ⓔ
		575V / 3ph / 60Hz	<input checked="" type="checkbox"/>	53	
Material		AISI 304	<input checked="" type="checkbox"/>	4	Ⓕ
		AISI 316	<input type="checkbox"/>	6	

1-Washing cycle: Dosing pump included ● : Par défaut  
 2-Heating with exchanger. On/off inlet valve included □ : En option



CLC01 - ⒶⒷ - ⒸⒹ - Ⓔ - Ⓕ  
 CLC01 - 1 2 - 3 3 - 53 - 4